

AUTO-FLEX[®] TC Power

Flexible tray rated power supply cable multiconductor / thermoset jacket / 2000V



Applications

AUTO-FLEX[®] TC tray rated power supply cable is designed and manufactured for use as a power supply cable from a welding timer or controller to the base of a robot in a resistance welding application. The cable provides a flexible tray rated solution that enhances the ease of installation when compared to standard tray cable. This cable can be used in many applications where flexibility is required and is suitable for use in exposed runs in accordance with the NEC.

Specifications and Ratings

- UL 1277 TypeTC-ER
- UL 44 Type RHW - 2 conductors
- ANSI/NEMA WC70 ICEA S-95-658
- Direct burial and sunlight resistant
- CSA AWM I/II A/B FT4



Options:

- 600 volt
- Shielded

Design Parameters

CONDUCTORS: Class K stranded, soft-drawn bare copper, per ASTM B-3 and ASTM B-172.

INSULATION: Heat and moisture-resistant, thermosetting crosslinked polyethylene meeting the requirements of ANSI/NEMA WC70 ICEA S-95-658. The insulation is acceptable for use in wet or dry locations at 90° C. The insulation thickness is in accordance with Table 17 of UL 44.

JACKET: Heat, moisture and sunlight resistant thermoset jacket, meeting the requirements of ANSI/NEMA WC70 ICEA S-95-658. The jacket thickness is in accordance with Table 11.3 of UL 1277.



© DRAKA - A Brand of The Prysmian Group. 2012 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued June 2012.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com

AUTO-FLEX® TC Power

Flexible tray rated power supply cable multiconductor / thermoset jacket / 2000V

Part Number	Conductor Number	Conductor Size	Stranding	Nominal Cable O.D. in (mm)	TC Ampacity ¹	Minimum Bend Diameter in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
031245	3	8 AWG	168/30	.845 (21.5)	55	7 (178)	405 (602)
031237	4	8 AWG	168/30	8 (203)	547 (814)	8 (203)	705 (1043)
031246	3	6 AWG	266/30	8 (203)	593 (882)	12 (305)	1740 (2575)
031238	4	6 AWG	266/30	1.090 (27.7)	60	11 (280)	746 (1110)
031247	3	4 AWG	413/30	1.110 (28.2)	95	11 (280)	795 (1183)
031239	4	4 AWG	413/30	1.220 (31.0)	76	12 (305)	1009 (1501)
031111	3	2 AWG	665/30	1.250 (31.8)	130	13 (330)	1115 (1659)
031240	4	2 AWG	665/30	1.380 (35.1)	104	14 (356)	1429 (2126)
031249	3	1/0 AWG	1045/30	1.535 (39.0)	170	15 (381)	1615 (2403)
031241	4	1/0 AWG	1045/30	1.695 (43.1)	136	17 (432)	2088 (3107)
031250	3	2/0 AWG	1323/30	1.690 (42.9)	195	17 (432)	2007 (2986)
031242	4	2/0 AWG	1323/30	1.935 (49.1)	156	19 (483)	2727 (4058)
031251	3	3/0 AWG	1672/30	1.845 (46.9)	225	18 (457)	2557 (3805)
031243	4	3/0 AWG	1672/30	2.040 (51.8)	180	24 (610)	3287 (4891)
031252	3	4/0 AWG	2107/30	2.085 (53.0)	260	25 (635)	3142 (4649)
031244	4	4/0 AWG	2107/30	2.310 (58.7)	208	28 (711)	4048 (6023)

¹Ampacity based on single cable in free air 30° C ambient, 90° C conductor temperature.

The data herein is approximate and subject to normal manufacturing tolerances.

These specifications are subject to change without notice.

© DRAKA - A Brand of The Prysmian Group. 2012 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued June 2012.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com