



**SINGLE CONDUCTOR 600 V SECONDARY UD XLP  
ALUMINUM UNDERGROUND DISTRIBUTION CABLE**

Specifications: UL 854 TYPE USE-2, ICEA S-105-692

CODE WORD	PHASE CONDUCTOR		PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS		
PRINCETON/XLP	6 7w	60	304037A	<b>\$289.00</b>
MERCER/XLP	4 7w	60	304835A	<b>345.00</b>
CLEMSON/XLP	2 7w	60	304142A	<b>421.00</b>
KENYON/XLP	1 19w	80		<b>498.00</b>
HARVARD/XLP	1/0 19w	80	304026A	<b>565.00</b>
YALE/XLP	2/0 19w	80	306056A	<b>684.00</b>
TUFTS/XLP	3/0 19w	80	305307A	<b>757.00</b>
BELOIT/XLP	4/0 19w	80	304182A	<b>881.00</b>
HOFSTRA/XLP	250 37w	95	306192A	<b>1165.00</b>
GONZAGA/XLP	300 37w	95	303382A	<b>1262.00</b>
RUTGERS/XLP	350 37w	95	303971A	<b>1469.00</b>
DARTMOUTH/XLP	400 37w	95		<b>1723.00</b>
EMORY/XLP	500 37w	95	303381A	<b>1967.00</b>
DUKE/XLP	600 61w	110		<b>2462.00</b>
FURMAN/XLP	700 61w	110		<b>2507.00</b>
SEWANEE/XLP	750 61w	110	304571A	<b>2560.00</b>
FORDHAM/XLP	1000 61w	110	305266A	<b>3449.00</b>

**SINGLE CONDUCTOR 600 V SECONDARY UD SUPERTUF®-XL  
ALUMINUM UNDERGROUND DISTRIBUTION CABLE**

Specifications: UL 854 TYPE USE-2, ICEA S-81-570

CODE WORD	PHASE CONDUCTOR		PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS		
PRINCETON/ST-XL	6 7w	60	304771A	<b>398.00</b>
MERCER/ST-XL	4 7w	60	301033A	<b>416.00</b>
CLEMSON/ST-XL	2 7w	60	301026A	<b>512.00</b>
KENYON/ST-XL	1 19w	80		<b>562.00</b>
HARVARD/ST-XL	1/0 19w	80	301099A	<b>670.00</b>
YALE/ST-XL	2/0 19w	80	301100A	<b>759.00</b>
TUFTS/ST-XL	3/0 19w	80	303010A	<b>804.00</b>
<b>*BELOIT/ST-XL</b>	4/0 19w	80	301101A	<b>942.00</b>
HOFSTRA/ST-XL	250 37w	95	301077A	<b>1344.00</b>
GONZAGA/ST-XL	300 37w	95		<b>1409.00</b>
<b>*RUTGERS/ST-XL</b>	350 37w	80	301102A	<b>1680.00</b>
<b>*EMORY/ST-XL</b>	500 37w	80	301103A	<b>2025.00</b>
SEWANEE/ST-XL	750 61w	110	305703A	<b>3029.00</b>
FORDHAM/ST-XL	1000 61w	110		<b>3962.00</b>

**\* INDICATES STANDARD STOCK ITEM**

NON-STOCK ITEMS SUBJECT TO 10,000 FT MINIMUM PRODUCTION QUANTITIES

PRYSMIAN'S TERMS & CONDITIONS APPLY TO ALL QUOTES AND ORDERS



Page 1 of 1  
 600V Aluminum UD  
 Effective: April 27, 2010

**DUPLEX 600 V SECONDARY UD XLP  
 ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
 THREE EXTRUDED YELLOW STRIPES**

Specifications: UL 854, ICEA S-105-692

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR	PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL		
BARD/XLP/3YS	8 7w	60	8 7w		<b>\$504.00</b>
CLAFLIN/XLP/3YS	6 7w	60	6 7w	303820A	<b>571.00</b>
DELGADO/XLP/3YS	4 7w	60	4 7w	303017A	<b>713.00</b>

**DUPLEX 600 V SECONDARY UD SUPTERTUF®  
 ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
 THREE EXTRUDED YELLOW STRIPES**

Specifications: UL 854, ICEA S-81-570

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR	PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL		
<b>*BARD/ST-XLP/3YS</b>	8 7w	30/30	8 7w	301104A	<b>\$518.00</b>
<b>*CLAFLIN/ST-XL/3YS</b>	6 7w	30/30	6 7w	301105A	<b>589.00</b>
<b>*DELGADO/ST-XL/3YS</b>	4 7w	30/30	4 7w	301106A	<b>712.00</b>

**\* INDICATES STANDARD STOCK ITEM**  
 NON-STOCK ITEMS SUBJECT TO 10,000 FT MINIMUM PRODUCTION QUANTITIES  
 PRYSMIAN'S TERMS & CONDITIONS APPLY TO ALL QUOTES AND ORDERS



**TRIPLEX 600 V SECONDARY UD XLP  
ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
THREE EXTRUDED YELLOW STRIPES**

Specifications: UL 854 TYPE USE-2, ICEA S-105-692

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR	PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL		
ERSKINE/XLP/3YS	6 7w	60	6 7w	303736A	<b>\$802.00</b>
VASSAR/XLP/3YS	4 7w	60	4 7w	303018A	<b>949.00</b>
STEPHENS/XLP/3YS	2 7w	60	4 7w	301801A	<b>1140.00</b>
RAMAPO/XLP/3YS	2 7w	60	2 7w	303029A	<b>1164.00</b>
<b>*BRENAU/XLP/3YS</b>	1/0 19w	80	2 7w	300328A	<b>1466.00</b>
BERGEN/XLP/3YS	1/0 19w	80	1/0 19w	303589A	<b>1599.00</b>
<b>*CONVERSE/XLP/3YS</b>	2/0 19W	80	1 19W	300329A	<b>1676.00</b>
HUNTER/XLP/3YS	2/0 19W	80	2/0 19W	303587A	<b>1808.00</b>
HOLLINS/XLP/3YS	3/0 19W	80	1/0 19w	303449A	<b>2030.00</b>
ROCKLAND/XLP/3YS	3/0 19w	80	3/0 19w		<b>2368.00</b>
<b>*SWEETBRIAR/XLP/3YS</b>	4/0 19W	80	2/0 19W	300330A	<b>2280.00</b>
MONMOUTH/XLP/3YS	4/0 19W	80	4/0 19W	303026A	<b>2552.00</b>
PRATT/XLP/3YS	250 37W	95	3/0 19W	301799A	<b>3113.00</b>
<b>*WESLEYAN/XLP/3YS</b>	350 37W	95	4/0 19W	300331A	<b>3871.00</b>
RIDER/XLP/3YS	500 37W	95	350 37W	303819A	<b>5465.00</b>

**TRIPLEX 600 V SECONDARY UD SUPERTUF®-XL  
ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
THREE EXTRUDED YELLOW STRIPES**

Specifications: UL 854 TYPE USE-2, ICEA S-81-570

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR	PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL		
<b>*ERSKINE/ST-XL/3YS</b>	6 7w	30/30	6 7w	301110A	<b>\$828.00</b>
<b>*VASSAR/ST-XL/3YS</b>	4 7w	30/30	4 7w	301116A	<b>1015.00</b>
<b>*STEPHENS/ST-XL/3YS</b>	2 7w	30/30	4 7w	301114A	<b>1199.00</b>
RAMAPO/ST-XL/3YS	2 7w	30/30	2 7w	303112A	<b>1231.00</b>
<b>*BRENAU/ST-XL/3YS</b>	1/0 19w	40/40	2 7w	301108A	<b>1510.00</b>
BERGEN/ST-XL/3YS	1/0 19w	40/40	1/0 19w	301107A	<b>1768.00</b>
<b>*CONVERSE/ST-XL/3YS</b>	2/0 19W	40/40	1 19W	301109A	<b>1727.00</b>
HUNTER/ST-XL/3YS	2/0 19W	40/40	2/0 19W	303113A	<b>1956.00</b>
<b>*HOLLINS/ST-XL/3YS</b>	3/0 19W	40/40	1/0 19w	301111A	<b>2159.00</b>
<b>*SWEETBRIAR/ST-XL/3YS</b>	4/0 19W	40/40	2/0 19W	301115A	<b>2349.00</b>
MONMOUTH/ST-XL/3YS	4/0 19W	40/40	4/0 19W	301112A	<b>2743.00</b>
<b>*WESLEYAN/ST-XL/3YS</b>	350 37W	40/40	4/0 19W	301117A	<b>3909.00</b>
WESLEYAN/ST-XL/3YS	350 37W	50/45	4/0 19W	301031A	<b>3985.00</b>
RIDER/ST-XL/3YS	500 37W	40/40	350 37W	303093A	<b>5443.00</b>
RIDER/ST-XL/3YS	500 37W	50/45	350 37W	303925A	<b>5633.00</b>

**\* INDICATES STANDARD STOCK ITEM**

NON-STOCK ITEMS SUBJECT TO 10,000 FT MINIMUM PRODUCTION QUANTITIES

PRYSMIAN'S TERMS & CONDITIONS APPLY TO ALL QUOTES AND ORDERS



**QUADRUPLEX 600 V SECONDARY UD XLP  
ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
THREE EXTRUDED YELLOW STRIPES**  
Specifications: UL 854 TYPE USE-2, ICEA S-105-692

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR	PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL		
TULSA/XLP/3YS	4 7w	60	4 7w	303509A	<b>\$1,241.00</b>
DYKE/XLP/3YS	2 7w	60	4 7w	303505A	<b>1503.00</b>
WITTENBURG/XLP/3YS	2 7w	60	2 7w	300306A	<b>1529.00</b>
NOTRE DAME/XLP/3YS	1/0 19w	80	2 7w	303508A	<b>2036.00</b>
PURDUE/XLP/3YS	1/0 19w	80	1/0 19w	304858A	<b>2169.00</b>
SYRACUSE/XLP/3YS	2/0 19w	80	1 19w	303507A	<b>2360.00</b>
LAFAYETTE/XLP/3YS	2/0 19w	80	2/0 19w		<b>2648.00</b>
SWARTHMORE/XLP/3YS	3/0 19w	80	1/0 19w		<b>3203.00</b>
DAVIDSON/XLP/3YS	3/0 19w	80	3/0 19w		<b>3406.00</b>
WAKE FOREST/XLP/3YS	4/0 19w	80	2/0 19w	303510A	<b>3396.00</b>
EARLHAM/XLP/3YS	4/0 19w	80	4/0 19w	304023A	<b>3454.00</b>
SLIPPERY ROCK/XLP/3YS	350 37w	95	4/0 19w		<b>5918.00</b>

**QUADRUPLEX 600 V SECONDARY UD SUPERTUF® -XL  
ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
THREE EXTRUDED YELLOW STRIPES**  
Specifications: UL 854 TYPE USE-2, ICEA S-81-570

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR	PART NUMBER	BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL		
TULSA/ST-XL/3YS	4 7w	30/30	4 7w		<b>\$1,305.00</b>
DYKE/ST-XL/3YS	2 7w	30/30	4 7w		<b>1548.00</b>
WITTENBURG/ST-XL/3YS	2 7w	30/30	2 7w		<b>1590.00</b>
<b>*NOTRE DAME/ST-XL/3YS</b>	1/0 19w	40/40	2 7w	301118A	<b>2251.00</b>
SYRACUSE/ST-XL/3YS	2/0 19w	40/40	1 19w		<b>2460.00</b>
<b>*WAKE FOREST/ST-XL/3YS</b>	4/0 19w	40/40	2/0 19w	301120A	<b>3499.00</b>
<b>*SLIPPERY ROCK/ST-XL/3YS</b>	350 37w	40/40	4/0 19w	301119A	<b>5710.00</b>
SLIPPERY ROCK/ST-XL/3YS	350 37w	50/45	4/0 19w		<b>6096.00</b>
WOFFORD/ST-XL/3YS	500 37w	40/40	350 37w	301025A	<b>8138.00</b>

**\* INDICATES STANDARD STOCK ITEM**

NON-STOCK ITEMS SUBJECT TO 10,000 FT MINIMUM PRODUCTION QUANTITIES  
PRYSMIAN'S TERMS & CONDITIONS APPLY TO ALL QUOTES AND ORDERS

**DUPLEX 600 V SECONDARY UD SUPERSEAL™**  
 ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
 THREE EXTRUDED YELLOW STRIPES

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR		BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	
CLAFLIN/SUPERSEAL/3YS	6 7w	60	6 7w	60	<b>\$ 660.00</b>
DELGADO/SUPERSEAL/3YS	4 7w	60	4 7w	60	<b>797.00</b>

**TRIPLEX 600 V SECONDARY UD SUPERSEAL™**  
 ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
 THREE EXTRUDED YELLOW STRIPES

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR		BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	
ERSKINE/SUPERSEAL/3YS	6 7w	60	6 7w	60	<b>\$ 927.00</b>
RAMAPO/SUPERSEAL/3YS	2 7w	60	2 7w	60	<b>1,379.00</b>
BRENAU/SUPERSEAL/3YS	1/0 19w	80	2 7w	60	<b>1,630.00</b>
BERGEN/SUPERSEAL/3YS	1/0 19w	80	1/0 19w	80	<b>1,909.00</b>
CONVERSE/SUPERSEAL/3YS	2/0 19W	80	1 19W	80	<b>1,865.00</b>
HUNTER/SUPERSEAL/3YS	2/0 19W	80	2/0 19W	80	<b>2,112.00</b>
*SWEETBRIAR/SUPERSEAL/3	4/0 19w	80	2/0 19w	80	<b>2,537.00</b>
MONMOUTH/SUPERSEAL/3YS	4/0 19w	80	4/0 19w	80	<b>2,962.00</b>
WESLEYAN/SUPERSEAL/3YS	350 37W	80	4/0 19W	80	<b>4,222.00</b>

**QUADRUPLEXED 600 V SECONDARY UD SUPERSEAL™**  
 ALUMINUM UNDERGROUND DISTRIBUTION CABLE  
 THREE EXTRUDED YELLOW STRIPES

CODE WORD	PHASE CONDUCTOR		NEUTRAL CONDUCTOR		BASE PRICE PER 1000 FEET
	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	SIZE AND STRANDING AWG/KCMIL	INSULATION THICKNESS MILS	
WITTENBURG/SUPERSEAL/3Y	2 7w	60	2 7w	60	<b>\$ 1,781.00</b>
NOTRE DAME/SUPERSEAL/3Y	1/0 19w	80	2 7w	60	<b>2,431.00</b>
WAKE FOREST/SUPERSEAL/3	4/0 19W	80	2/0 19W	80	<b>3,779.00</b>
SLIPPERY ROCK/SUPERSEAL	350 37W	80	4/0 19W	80	<b>6,583.00</b>

\* INDICATES STANDARD STOCK ITEM

NON-STOCK ITEMS SUBJECT TO 10,000 MINIMUM PRODUCTION QUANTITIES.

PRYSMIAN'S TERMS & CONDITIONS APPLY TO ALL QUOTES AND ORDERS.