

STABILOY® BRAND
RESIDENTIAL ALUMINUM BUILDING WIRE
Published List Prices
 Net Weight of Conductor Per Shipment and Destination

Type SE Style U - STABILOY® BRAND*

SIZE	WT/MFT	\$/MFT
8-8-8	103	\$3,102.83
6-6-6	140	\$3,654.94
4-4-6	181	\$3,754.02
4-4-4	195	\$4,100.21
2-2-4	254	\$4,916.11
2-2-2	278	\$5,356.25
1-1-1	349	\$7,257.55
1/0-1/0-2	387	\$7,264.79
1/0-1/0-1/0	417	\$7,626.98
2/0-2/0-1	468	\$8,190.92
2/0-2/0-2/0	516	\$8,763.03
4/0-4/0-2/0	681	\$11,294.38
4/0-4/0-4/0	760	\$12,265.75

Type SE Style R - STABILOY® BRAND*

3 Conductor with Ground

SIZE	WT/MFT	\$/MFT
8-8-8-8	127	\$3,673.55
6-6-6-6	178	\$4,158.94
4-4-4-6	236	\$5,124.34
2-2-2-4	340	\$6,866.23
1-1-1-3	426	\$8,936.74
1/0-1/0-1/0-2	526	\$9,727.80
2/0-2/0-2/0-1	625	\$11,779.59
3/0-3/0-3/0-1/0	762	\$14,528.60
4/0-4/0-4/0-2/0	934	\$16,336.55
250-250-250-3/0	1118	\$18,876.76
300-300-300-4/0	1324	\$22,548.84

Type SE Style R - STABILOY® BRAND*

2 Conductor with Ground

SIZE	WT/MFT	\$/MFT
8-8-8†	96	\$2,958.58
6-6-6†	135	\$3,108.44
4-4-6†	174	\$3,638.10
4-4-4†	190	\$3,968.02
2-2-4†	250	\$4,942.82
2-2-2†	276	\$5,005.86
1-1-1†	342	\$6,737.54
1/0-1/0-2†	376	\$6,955.07
1/0-1/0-1/0†	414	\$7,265.63
2/0-2/0-1†	451	\$7,761.03
2/0-2/0-2/0†	513	\$8,841.90
4/0-4/0-2/0†	679	\$11,227.01
4/0-4/0-4/0†	758	\$11,800.61

Type SE Style R - STABILOY® BRAND*

4 Conductor with Ground

SIZE	WT/MFT	\$/MFT
6-6-6-6-6†	224	\$6,708.11
4-4-4-4-6†	298	\$7,732.52
2-2-2-2-4†	431	\$11,261.57
1-1-1-1-3†	537	\$14,557.07
1/0-1/0-1/0-1/0-2†	667	\$15,940.90
2/0-2/0-2/0-2/0-1†	809	\$18,740.00
3/0-3/0-3/0-3/0-1/0†	994	\$23,142.08
4/0-4/0-4/0-4/0-2/0†	1185	\$27,032.66
250-250-250-250-3/0†	1420	\$32,373.13
300-300-300-300-4/0†	1678	\$39,604.32

Mobile Home Feeder Cable - Green Ground*

SIZE	WT/MFT	\$/MFT
2-2-4-6	291	\$6,235.15
2-2-2-4	340	\$6,650.10
2/0-2/0-1-4	547	\$10,153.77
2/0-2/0-2/0-1	663	\$11,807.77
4/0-4/0-2/0-4	772	\$13,123.47
4/0-4/0-4/0-2/0	974	\$15,947.00

Orders are subject to acceptance by Prysmian Group, and subject to Prysmian Group's standard Terms and Conditions.
 †Items subject to minimum production quantities.