



## PRODUCT INFORMATION SHEET

### 3SSF Battery Cable

125°C - Standard Wall - Standard Stranding - Flexible Insulation with Bare Copper Conductors

#### Features

Copper Conductors per ASTM B3 and ASTM B33  
Insulation Material: XLPE (Cross-linked Polyolefin)  
RoHS Compliant

#### Applications

Low tension cables for -40°C to 125°C  
Nominal system voltage up to 60 V DC  
Temperature Class 3 -40°C to 125°C

#### Compliance

Ford ES-AU5T-1A348-AA Rev J

#### Product Options

Colors Red or Black, Others available upon request  
Packaging Options: Reels, various sizes and disposal or recyclable

Conductor Size	Number of Strands	Maximum Strand Diameter	Conductor Resistance, Maximum	Insulation Thickness, Minimum	Cable OD, Minimum	Cable OD, Maximum
mm <sup>2</sup>	± 5%	mm	mΩ/m	mm	mm	mm
120	1726	0.31	0.153	1.28	17.70	19.70

Rev 0 (2020-11-23)

Written by: AJTurnbull