


## Buffer Tube Slitter

Hand tool for easy mid-span access to buffer tubes



### Features and Benefits

#### Precision Engineering

- No adjustment or tuning required
- Depth of cut is optimized for each specific tube size
- Buffer tube walls are slit open without risk of fiber damage

#### Rugged Construction

- Body is machined from solid aluminum
- Built for use in the real world

#### Recessed Blades

- Cutting surfaces are protected
- Minimal blade projection enhances tool safety

#### Compact and Lightweight

- Easy to transport
- Saves room in the toolkit

#### Clearly and Permanently Marked

- Both halves of the tool are engraved with size information
- Correct slitting direction is clearly marked
- All critical information is machined directly into the tool and cannot rub off

#### Heavy Duty Retaining Cord

- Keeps the two halves together for easier location and use

#### Buffer Tube Sizing Guides

- Allows tube dimensions to be checked without applying the tool

#### Quick, Safe and Easy Mid-Span Access

- Saves time, avoids injuries and protects fiber assets

#### Economical

- Pays for itself by avoiding dangerous work practices
- Just as effective and more durable than units costing many times more

## Buffer Tube Slitter

Hand tool for easy mid-span access to buffer tubes



### PART NUMBERS

Size Range	Applicable Cable Designs*	Part Number
1.9 mm	ActionLink™	9000090000
2.5mm	Aerolink™ ADSS	9000090001
2.65 mm	AeroLink™ Figure-8, FlexLink™, FirstLink™	9000090017
2.8 - 3.1 mm	CentraLink™, ResiLink™ (all types)	9000090014
4.1 mm	CentraLink™, CampusLink™	9000090003
6.2 mm	BundleLink™, FusionLink™, MassLink™, UniLink™	9000090004
6.8 mm	Various Ribbon Cables	9000090011
7.9 mm	BundleLink™, MassLink™	9000090009
8.4 mm	FusionLink™, UniLink™	9000090005
8.7 mm	Miscellaneous Ribbon Cables	9000090013
9.5 mm	FusionLink™	9000090007
9.9 mm	FusionLink™	9000090019
10.6 mm	FusionLink™	9000090010
11.0 mm	FusionLink™	9000090006
12.3 mm	FusionLink™	9000090012
14.3 mm	FusionLink™	9000090018
15.4 mm	FusionLink™	9000090038

Spare Parts	Quantity Per Tool	Part Number
Blades (2)	2	9000090015
Retainer Cord	1	9000090008

\*Note: Always check the current datasheet for the cable you are using to verify the buffer tube size prior to selecting a buffer tube slitter.

© DRAKA & PRYSMIAN - Brands of The Prysmian Group. 2013 All Right Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless specifically authorized by Prysmian Group. Issued April 2013.

### Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | [www.prysmiangroup.com](http://www.prysmiangroup.com)

### Sales:

2512 Penny Road | Claremont, NC 28610 | +1-800-879-9862 | +1-828-459-8895