



ezTOOLS™ | Buffer Tube Midspan Access Tool

Buffer Tube Midspan Access Tool (1.8 to 3.0 mm)



The simplest and most reliable midspan access tool for loose buffer tubes.

Overview

Prysmian's ezACCESS | Buffer Tube Access Tool provides quick and easy access to fibers every time. Designed for midspan entry in buffer tubes to access fibers, this is the one-stop tool for the veteran or the new installer.

Specially designed inserts hold the buffer tube firmly in place where a precision-ground blade "shaves" only the tube wall - providing reliable access without damage to the fiber or coating. An industry study revealed that Prysmian's ezACCESS Buffer Tube Access tool provides the most consistent, safe and reliable access while other tools frequently damaged fibers and / or coatings.

Interchangeable labeled inserts support a wide variety of buffer tubes sizes used for different fiber counts and cable designs. The tool's thick gauge steel alloy construction and a hard shell tote case mean years of reliable field use. These interchangeable inserts change in and out within 15 seconds.

Kit Contains

- 1 Buffer Tube Access Tool with Carrying Case
- 3 Inserts (2.5mm / 2.7mm / 3.0mm - common sizes)
- Spare parts: 1 spare blade, 1 socket head screw

Product Snapshot

- Applications** Reliable midspan entry to access fibers in loose tube cables. Easy change inserts for a variety of manufacturers' tube sizes.
- Cable Types** Loose Tube, ADSS, Microduct & Specialty
- Tool Type** One Hand Operation / Shaving Action
Quick Change Inserts / Rugged
- Options** Kit (1 tool, 3 inserts, accessories) / Inserts (10) to fit a Variety of Buffer Tube Sizes

Content may be subject to change without notification

Features and Benefits

Reliable Tube Access

- Reliable and repeatable access to fibers without damage
- Lab tested & field proven
- No calibration required
- Rugged and built to last

Simple & Flexible Support of Multiple Size Buffer Tubes

- Multi-purpose tool supports up to 10 insert sizes
- 15 second change out of inserts
- Cleaner midspan access

ezTOOLS™ | Buffer Tube Midspan Access Tool

Buffer Tube Midspan Access Tool (1.8 to 3.0 mm)

Ordering Guide

Item Description	Part Number
Tool Kit Includes: 1 Buffer Tube Access Tool with carrying case 3 Inserts (2.5mm / 2.7mm / 3.0mm - common sizes) Spare Parts: 1 spare blade, 1 spare socket head screw Accessories: 1 fiber spatula, 1 allen wrench	20021562
Spare Parts Kit Includes: 2 blades 2 socket head screws 1 fiber spatula	20021563

Inserts for Draka Products

Tube Diameter mm	Fibers Per Tube	Draka Cable Description	Part Number (Tool)
1.9	12	ezMICROduct™, ezDROP™ Flat (≤ 6 fibers), ezDROP Figure 8	20021564
2.0	12	LT20	20022885
*2.5	12	ExpressLT™ Gel & Gel-Free	20021566
2.6	12	Loose Tube Indoor-Outdoor (> 36 fibers) ADSS Long Span (2 to 84 fibers)	20021602
*2.7	12	ezPREP Loose Tube Gel & Gel-Free (discontinued April 2010)	20030089
*3.0	12	ExtremeLink™ Loose Tube ezSPAN™ ADSS Loose Tube Figure 8	20021569
3.0	24	ADSS Long Span (96-288 fibers, 24 fibers / tube) Loose Tube High Count (> 288 fibers, 24 fibers / tube)	20021570

Other Inserts Available

Tube Diameter mm	Fibers per Tube	Draka Cable Description	Part Number (Tool)
1.8	12	Microduct Cable (reduced diameter - discontinued)	20022986
2.2	12	Microduct Cable (custom)	20023032
2.4	24	Sewer Cable (specialty)	20021565

*Replacement insets are also available for purchase individually.

© DRAKA & PRYSMIAN - Brands of The Prysmian Group. 2013 All Right Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless specifically authorized by Prysmian Group. Issued May 2013.