


Buffer Tube Slitter

Hand tool for easy mid-span access to buffer tubes



Features and Benefits

Precision Engineering

- No adjustment or tuning required
- Depth of cut is optimized for each specific tube size
- Buffer tube walls are slit open without risk of fiber damage

Rugged Construction

- Body is machined from solid aluminum
- Built for use in the real world

Recessed Blades

- Cutting surfaces are protected
- Minimal blade projection enhances tool safety

Compact and Lightweight

- Easy to transport
- Saves room in the toolkit

Clearly and Permanently Marked

- Both halves of the tool are engraved with size information
- Correct slitting direction is clearly marked
- All critical information is machined directly into the tool and cannot rub off

Heavy Duty Retaining Cord

- Keeps the two halves together for easier location and use

Buffer Tube Sizing Guides

- Allows tube dimensions to be checked without applying the tool

Quick, Safe and Easy Mid-Span Access

- Saves time, avoids injuries and protects fiber assets

Economical

- Pays for itself by avoiding dangerous work practices
- Just as effective and more durable than units costing many times more

Buffer Tube Slitter

Hand tool for easy mid-span access to buffer tubes



PART NUMBERS

| Size Range | Applicable Cable Designs* | Part Number |
|--------------|---|-------------|
| 1.9 mm | ActionLink™ | 9000090000 |
| 2.5mm | Aerolink™ ADSS | 9000090001 |
| 2.65 mm | AeroLink™ Figure-8, FlexLink™, FirstLink™ | 9000090017 |
| 2.8 - 3.1 mm | CentraLink™, ResiLink™ (all types) | 9000090014 |
| 4.1 mm | CentraLink™, CampusLink™ | 9000090003 |
| 6.2 mm | BundleLink™, FusionLink™, MassLink™, UniLink™ | 9000090004 |
| 6.8 mm | Various Ribbon Cables | 9000090011 |
| 7.9 mm | BundleLink™, MassLink™ | 9000090009 |
| 8.4 mm | FusionLink™, UniLink™ | 9000090005 |
| 8.7 mm | Miscellaneous Ribbon Cables | 9000090013 |
| 9.5 mm | FusionLink™ | 9000090007 |
| 9.9 mm | FusionLink™ | 9000090019 |
| 10.6 mm | FusionLink™ | 9000090010 |
| 11.0 mm | FusionLink™ | 9000090006 |
| 12.3 mm | FusionLink™ | 9000090012 |
| 14.3 mm | FusionLink™ | 9000090018 |
| 15.4 mm | FusionLink™ | 9000090038 |

| Spare Parts | Quantity Per Tool | Part Number |
|---------------|-------------------|-------------|
| Blades (2) | 2 | 9000090015 |
| Retainer Cord | 1 | 9000090008 |

*Note: Always check the current datasheet for the cable you are using to verify the buffer tube size prior to selecting a buffer tube slitter.

© DRAKA & PRYSMIAN - Brands of The Prysmian Group. 2013 All Right Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless specifically authorized by Prysmian Group. Issued April 2013.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales:

2512 Penny Road | Claremont, NC 28610 | +1-800-879-9862 | +1-828-459-8895