



**Prysmian Fiber Cable**  
with 3-Day Rapid Shipment



**800-879-9862**  
**800-669-0808**

Updated March 22, 2018

## RISER | PLENUM | INDOOR/OUTDOOR

Always In Stock | Ships in 3 Days | No Cut Fee Over 1640 Feet

# EXTERNAL

Fiber Count	Fiber Type	Cable Type	Cable Design	Indoor or I/O	Flame Rating	Armored (Yes / No)	Prysmian Product Catalog #	Prysmian Data Sheet #
6	Singlemode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-00-HB-006-EA	DS042
12	Singlemode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-00-HB-012-EB	DS042
24	Singlemode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-00-HB-024-EB	DS042
48	Singlemode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-12-HB-048-EA	DS042
6	Singlemode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-00-HB-006-EB	DS042
12	Singlemode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-00-HB-012-EB	DS042
24	Singlemode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-00-HB-024-EA	DS042
48	Singlemode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-12-HB-048-EA	DS042
6	OM3 Multimode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-00-G3-006-M3	DS042
12	OM3 Multimode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-00-G3-012-M3	DS042
24	OM3 Multimode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-00-G3-024-M3	DS042
48	OM3 Multimode	Tight Buffer	Distribution	Indoor	Plenum	No	F-800-12-G3-048-M3	DS042
6	OM3 Multimode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-00-G3-006-M3	DS042
12	OM3 Multimode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-00-G3-012-M3	DS042
24	OM3 Multimode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-00-G3-024-M3	DS042
48	OM3 Multimode	Tight Buffer	Distribution	Indoor	Riser	No	F-400-12-G3-048-M3	DS042
6	Singlemode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-00-HB-006-EA	DS024
12	Singlemode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-00-HB-012-EB	DS024
24	Singlemode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-00-HB-024-EA	DS024
48	Singlemode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-12-HB-048-EB	DS024
6	OM3 Multimode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-00-G3-006-M3	DS024
12	OM3 Multimode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-00-G3-012-M3	DS024
24	OM3 Multimode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-00-G3-024-M3	DS024
48	OM3 Multimode	Tight Buffer	Distribution	I/O	Riser	No	F-C1181-12-G3-048-M3	DS024
12	Singlemode	Tight Buffer	Distribution	Indoor	Plenum	Yes - Interlock	F-800AJ-00-HB-012-EB	DS182
24	Singlemode	Tight Buffer	Distribution	Indoor	Plenum	Yes - Interlock	F-800AJ-00-HB-024-EB	DS182
6	OM3 Multimode	Tight Buffer	Distribution	Indoor	Plenum	Yes - Interlock	F-800AJ-00-G3-006-M3	DS182
12	OM3 Multimode	Tight Buffer	Distribution	Indoor	Plenum	Yes - Interlock	F-800AJ-00-G3-012-M3	DS182
24	OM3 Multimode	Tight Buffer	Distribution	Indoor	Plenum	Yes - Interlock	F-800AJ-00-G3-024-M3	DS182
12	Singlemode	MicroFiber	3mm Single Unit	Indoor	Plenum	No	F-MFC00-00-B1-012-E1	DS055B
24	Singlemode	MicroFiber	3mm Single Unit	Indoor	Plenum	No	F-MFC30-00-B1-024-E1	DS055B
12	OM3 Multimode	MicroFiber	3mm Single Unit	Indoor	Plenum	No	F-MFC00-G3-012-M3	DS055B
24	OM3 Multimode	MicroFiber	3mm Single Unit	Indoor	Plenum	No	F-MFC30-00-G3-024-M3	DS055B
96	Singlemode	MicroFiber	2mm Multi Unit	Indoor	Plenum	No	F-MFC20-12-B1-096-E1	DS055A
144	Singlemode	MicroFiber	2mm Multi Unit	Indoor	Plenum	No	F-MFC20-12-B1-144-E1	DS055A
2	Singlemode	Tight Buffer	2mm Zipcord	Indoor	Riser	No	F-520Z-00-CU-002-EA	DS043
2	Singlemode	Tight Buffer	2mm Zipcord	Indoor	Plenum	No	F-820Z-00-CU-002-EA	DS043
2	OM3 Multimode	Tight Buffer	2mm Zipcord	Indoor	Riser	No	F-520Z-00-G3-002-M3	DS043
2	OM3 Multimode	Tight Buffer	2mm Zipcord	Indoor	Plenum	No	F-820Z-00-G3-002-M3	DS043
12	Singlemode	Loose Tube	Central Unit	I/O	Riser	No	F-DRLDB-00-HB-012-E3	DS022
24	Singlemode	Loose Tube	Multi Unit	I/O	Riser	No	F-DRLDB-12-HB-024-E3	DS022
48	Singlemode	Loose Tube	Multi Unit	I/O	Riser	No	F-DRLDB-12-HB-048-E1	DS022

Email: [Comm.Cables2@prysmiangroup.com](mailto:Comm.Cables2@prysmiangroup.com) or [Comm.Cables@prysmiangroup.com](mailto:Comm.Cables@prysmiangroup.com)