


## ezTOOLS™ | UniSaver Midspan Access Tool

Ribbon Tube Midspan Access Tool for Legacy Draka Ribbon Cable (6.3 to 14.0 mm)



*Reliable midspan access tool for legacy Draka ribbon and buffer tubes.*

### Overview

Prysmian's Ribbon Central Tube Unishaver provides quick and easy midspan access to legacy Draka ribbon central tubes. This specially designed tool holds the buffer tube firmly in place where a precision blade "shaves" only the tube wall, providing access to ribbon fibers without damage to the fiber or coating. The new kit comes with the shell and a choice of inserts for various size tube diameters. Inserts are color coded and engraved to make easy selection of the right insert for the job.

The UniShaver Tool is designed to open tubes of 6.3 mm (0.24 inches) diameter and larger, and is typically used with legacy Draka central tube and ribbon in loose tube ribbon cables. Select the correct tool size, open the palm-size holder, calibrate the blade depth, and go.

### Kit Contains

- Shell
- Inserts
- Calibration pin gauge
- Carry case
- Replacement blade & screws

### Product Snapshot

- |                     |   |
|---------------------|---|
| <b>Applications</b> | Opens the tubes in legacy Draka ribbon fiber optic cable /reliable midspan entry to fiber ribbons |
| <b>Cable Types</b>  | Central loose tube and loose tube ribbon  |
| <b>Tool Type</b>    | One hand operation/shaving action (6.3 to 14.0 mm)  |
| <b>Options</b>      | Inserts to fit a variety of tube sizes from 6.3 to 14.0 mm  |

### Features and Benefits

#### Reliable Tube Access

- Reliable and repeatable access to fibers without damage
- Lab tested and field proven
- Easy and infrequent calibration
- Rugged and built to last

#### Simple & Flexible Support of Multiple Tube Size

- Inserts available for tube sizes 6.3 to 14.0 mm
- Inserts fit into a common size shell
- Cleaner midspan access

## ezTOOLS™ | Unishaver Ribbon Midspan Access Tool

Ribbon Tube Midspan Access Tool for Legacy Draka Ribbon Cable (6.3 to 14.0 mm)

### Specifications

Tool Dimensions	Case Dimensions (H x W x D) inches (mm)	Shipping Weight lbs / kg
1.5" outer diameter x 2.25" length (39 mm x 57 mm)	8.5 x 6 x 2.75 (216 x 152 x 70)	2 (0.9)

### Ordering Guide

The Prysmian UniShaver Access Tool is sold in kits containing one to three inserts, tailored to the tube sizes you are working with. For cables with different tube sizes than those shown, contact customer service at 800.879.9862.

#### Kits with Single Tools

Tube Diameter mm (inches)	Color	Draka Cable Type	Fiber Count	Part Number (Tool)
6.3 (0.25/0.24)	Blue	ezRIBBON   Central Tube Ribbon ezRIBBON   Loose Tube Ribbon ezRIBBON   Central Tube Gel-Free ezUNITUBE (Armored) - discontinued ezUNITUBE (Dielectric) - discontinued	12 to 72 288 to 432 12 to 48 26 to 48 2 to 48	10024922
7.0 (0.28)	Black	ezRIBBON   Loose Tube Ribbon	288 to 432 (thru 2006)	10024928
7.9 (0.31)	Orange	ezRIBBON   Central Tube Ribbon ezRIBBON   Loose Tube Ribbon ezUNITUBE	84 to 144 576 to 864 50 to 96	10024923
9.1 (0.36)	Brown	ezRIBBON   Central Tube Gel-Free	60 to 144	10031890
10.4 (0.41)	Green	ezRIBBON   Central Tube Ribbon	156 to 216	10024924
11.7 (0.46)	Black	ezRIBBON   Central Tube Gel-Free	156 to 216	10031889
12.2 (0.48)	Blue	ezRIBBON   Central Tube Gel-Free	156 to 216	10027514
14.0 (0.55)	Yellow	ezRIBBON   Central Tube Ribbon	240 to 432	10030432
14.5 (0.57)	Violet	ezRIBBON   Central Tube Ribbon Gel-Free	240 to 432	10032562

#### Kits with 2 Tools - Kit with 2 shells & 2 inserts

Tube Diameter mm (inches)	Color	Draka Cable Type	Fiber Count	Part Number (Tool)
6.3 & 7.9 (0.25 & 0.31)	Blue & Orange	see above descriptions		10024925
7.9 & 10.4 (0.31 & 0.41)	Orange & Green	see above descriptions		10025926

Replacement shells & inserts are also available for purchase individually.

© DRAKA & PRYSMIAN - Brands of The Prysmian Group 2015 All Right Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless specifically authorized by Prysmian Group. Issued September 2015.

#### Prysmian Group

700 Industrial Drive | Lexington, SC 29072

+1-800-879-9862 | +1-800-669-0808 | website: [na.prysmiangroup.com/telecom](http://na.prysmiangroup.com/telecom)