

# Here's a premium rubber outdoor cord with a new level of visibility.

FrogHide is more than a funny name. It's the most durable rubber outdoor cord on the market, the most flexible, and it *now features a connector end that lights up to indicate the power is on.* 

The three-conductor grounded FrogHide extension cord uses the most advanced rubber technology available anywhere. A technology that bonds cap and connector to the cord to prevent cord pull-out. And a heavy duty strain relief is built-in for lasting strength, even in rough applications.

FrogHide's improved electrical connections ensure more contact area between blades and receptacles, resulting in longer cord life.

There's more: FrogHide's distinctive green color is complemented by an exclusive personal identification system and a limited lifetime warranty.

#### Use FrogHide anywhere:

- Indoor & Outdoor Applications
- Hot & Cold Temperatures
- Abusive Environments
- Harsh Weather Conditions

FrogHide's like no other outdoor cord. It is resistant to oil, water, ozone and chemicals. It out-performs other extension cords in low and room temperatures, and does not soften when exposed to heat.

### **FEATURES**

	I LITTORES
Ultra Flex Cord	FrogHide's state-of-the-art rubber technology provides for more flexibility than any cord on the market.
Connector Lights Up for Safety	Female end of the FrogHide extension cord includes a power indicator that glows letting you know when there's power to the end of the cord. Just one more safety and convenience feature designed to help protect you and your tools.
Bonded Cap and Connector	FrogHide cord is bonded to the ends with a heavy-duty strain relief built-in for lasting strength. There's no more worry about cord pull-out.
Improved Electrical Connections	More contact area between blades and contact receptacles ensure longer cord life.
Distinctive Green Color	FrogHide looks like no other cord. Its bright green color is easy to see on the job — anytime, anywhere.
Identification System	It's simple to permanently mark your FrogHide cord with your name.
Limited Lifetime Warranty	We are so satisfied with the FrogHide cord we guarantee you will be too.
Specifications	FrogHide is UL Listed and meets all appropriate OSHA requirements.

## LIMITED LIFETIME WARRANTY

#### Flexible

FrogHide cords are constructed to be more flexible than any other outdoor cord... and to stay flexible in any condition or environment.

#### Visible

When power is running through your FrogHide cord, the connector end lights up. This safety and convenience feature is designed to help protect you and your tools.

#### Durable

FrogHide's bonded cord and heavy-duty strain relief provide long-lasting strength, even in the roughest of applications. Its improved electrical connections ensure more contact area between blades and receptacles, resulting in longer cord life.

## FrogHide® Ultra Flex®




#### **Extension Cord Performance Guide**

	FrogHide®	All Weather	Lifetime Plus®	Safety Orange®
Low Temperature Flex	Excellent	Very Good	Good	Fair
Room Temperature Flex	Excellent	Very Good	Very Good	Good
Oil Resistance	Excellent	Very Good	Very Good	Fair
Cap/Cord Bonding	Excellent	Excellent	Very Good	Good
Abrasion Resistance	Very Good	Very Good	Very Good	Very Good
Chemical Resistance	Excellent	Very Good	Very Good	Very Good
Heat Softening	Excellent	Fair	Fair	Fair
Water Resistance	Excellent	Excellent	Very Good	Good
Flame Resistance	Very Good	Very Good	Very Good	Very Good
Lighted Connector	Yes	No*	Yes	No

<sup>\*</sup>All Weather Lighted Connector coming in Q2 2021

## **Flexibility**





#### **Master Cartons**

Catalog Number	Description			Carton Qty.	UPC Code
06425.63.06L	25'	14/3	SJOW	10	079407 064250
06450.63.06L	50'	14/3	SJOW	6	079407 064502
06400.63.06L	100'	14/3	SJOW	4	079407 064007
06225.61.06L	25'	12/3	SJOW	6	079407 062256
06250.61.06L	50'	12/3	SJOW	4	079407 062508
06200.61.06L	100'	12/3	SJOW	2	079407 062003

## **General Cable**