

Type RHH / RHW-2 / USE-2 EPR Insulated Wire

Ethylene propylene rubber (EPR) / single conductor / 14 AWG to 500 KCMIL / 600V



Applications

Draka's Type RHH/RHW-2/USE-2 cable is suitable for various commercial and industrial applications. These cables may be installed in wet or dry locations, indoors or outdoors, in raceways, underground ducts (ask about our preinstalled cable-in-conduit products), aerial or direct buried.

Draka's Type RHH/RHW-2/USE-2 cable is NEC-compliant for continuous operations at 90° C in wet and dry locations, 130° C for emergency overload conditions and 250° C for short circuit conditions.

Specifications and Ratings

- UL Type RHH or RHW-2 or USE-2
- The insulation is suitable for use in wet or dry locations at a temperature not exceeding 90° C
- -40° C rated
- Direct burial
- Oil & gas resistant II
- FT2
- VW-1 CT USE (#1/0 AWG and larger) constructions are available
- RoHS compliant

Design Parameters

CONDUCTORS: Class B, soft drawn, bare copper per ASTM B3 and ASTM B8. Both tinned copper conductors and extra-flexible conductors are available as options.

INSULATION: Heat and moisture resistant crosslinked polyethylene (XLPE) meeting the requirements ICEA S-95-658 (NEMA WC 70), UL 44 for Type RHH and RHW-2 wires and UL 854 for Type USE-2. The insulation is suitable for use in wet or dry locations at a conductor temperature not exceeding 90° C for normal operation.

ASSEMBLY: Single conductor cables can be paralleled or multiplexed for more efficient installations. Single conductor cables can also be pre-installed in conduit.



Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com
One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381

Type RHH / RHW-2 / USE-2 EPR Insulated Wire

Ethylene propylene rubber (EPR) / single conductor / 14 AWG to 500 KCMIL / 600V

Conductor Size AWG (mm ²)	Strand Class	Strands	Nominal Insulation Thickness in (mm)	Nominal Cable O.D. in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
14 AWG (2.08)	Class B	7	.045 (1.1)	0.170 (4.3)	22 (33)
12 AWG (3.31)	Class B	7	.045 (1.1)	0.190 (4.8)	30 (45)
10 AWG (5.26)	Class B	7	.045 (1.1)	0.215 (5.5)	44 (65)
8 AWG (8.37)	Class B	7	.060 (1.5)	0.275 (7.0)	72 (107)
6 AWG (13.3)	Class B	7	.060 (1.5)	0.310 (7.9)	106 (158)
4 AWG (21.2)	Class B	7	.060 (1.5)	0.360 (9.1)	160 (238)
2 AWG (33.6)	Class B	7	.060 (1.5)	0.420 (10.7)	243 (362)
1 AWG (42.4)	Class B	19	.080 (2.0)	0.500 (12.7)	311 (463)
1/0 AWG (53.5)	Class B	19	.080 (2.0)	0.540 (13.7)	387 (576)
2/0 AWG (67.4)	Class B	19	.080 (2.0)	0.585 (14.9)	492 (732)
3/0 AWG (85.0)	Class B	19	.080 (2.0)	0.635 (16.1)	611 (909)
4/0 AWG (107)	Class B	19	.080 (2.0)	0.695 (17.7)	740 (1101)
250 KCMIL (127)	Class B	37	.095 (2.4)	0.770 (19.6)	882 (1312)
350 KCMIL (177)	Class B	37	.095 (2.4)	0.875 (22.2)	1213 (1805)
500 KCMIL (253)	Class B	37	.095 (2.4)	1.005 (25.5)	1702 (2533)

These cables are made in the USA, meeting ISO 9001 Quality Standard & 14001 Environmental Standard.

The data herein is approximate and subject to normal manufacturing tolerances. These specifications are subject to change without notice.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com

One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381