


Armored Aerial Signal Cable

multiple EPR insulated conductors / 14, 10, 9, & 6 AWG / PE jacket / 600 and 2000 volt



Applications

These are multi-conductor 600 & 2000 volt signal cables specifically designed for use in railroad signal and control circuits in accordance with the AREMA Signal Manual. They are intended for aerial or duct installation for use wherever long service life is required. They consist of ethylene propylene rubber (EPR) insulated conductors, a cushion layer, helically-applied bronze armor and a polyethylene outer jacket.

Specifications and Ratings

- AREMA Signal Parts 10.3.16, 10.3.19 and 10.3.21
- ICEA S-95-658 (NEMA WC 70)

Construction

CONDUCTOR: Solid soft drawn, bare or tinned copper per ASTM B258 and B33.

INSULATION: Heat and moisture resistant EPR meeting the requirements of AREMA C&S Manual Part 10.3.19, suitable for a maximum continuous operating temperature of 90°C.

CIRCUIT IDENTIFICATION: Black conductors with number print: (1-ONE, 2-TWO, 3-THREE, etc.). One black conductor with a red stripe serves as a tracer.

ASSEMBLY: The insulated circuit conductors are cabled together with non-hygroscopic fillers as needed. The cable core is wrapped in a binder tape.

CUSHION LAYER: The insulated circuit conductors are cabled together with non-hygroscopic fillers as needed. The cable core is wrapped in a binder tape.

ARMOR: 10 mil thick bronze tape helically-applied with a minimum overlap of 20%. An optional 10 mil thick bronze tape corrugated and longitudinally applied with a minimum overlap of 12.5% is available upon request.

OVERALL JACKET: Heat and moisture-resistant black polyethylene (PE) meets the requirements of AREMA C&S Manual Part 10.3.21. Neoprene and LSZH XLPO are available. Optional ripcord placed underneath the overall jacket is available upon request.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444
One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381

Armored Aerial Signal Cable

multiple EPR insulated conductors / 14, 10, 9, & 6 AWG / PE jacket / 600 and 2000 volt

Part Number	Number of Conductors	Rated Voltage	Conductor Size	Average Insulation Thickness in (mm)	Average Jacket Thickness in (mm)	Cable O.D. in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
192105	5	600	14 AWG	.045 (1.1)	.080 (2.0)	0.760 (19.3)	328 (489)
192107	7	600	14 AWG	.045 (1.1)	.080 (2.0)	0.815 (20.7)	393 (586)
192112	12	600	14 AWG	.045 (1.1)	.095 (2.4)	1.040 (26.4)	604 (900)
192119	19	600	14 AWG	.045 (1.1)	.095 (2.4)	1.180 (30.0)	824 (1228)
192305	5	600	10 AWG	.045 (1.1)	.080 (2.0)	0.865 (22.0)	475 (708)
192307	7	600	10 AWG	.045 (1.1)	.095 (2.4)	0.960 (24.4)	608 (906)
192312	12	600	10 AWG	.045 (1.1)	.095 (2.4)	1.200 (30.5)	931 (1387)
192405	5	600	9 AWG	.045 (1.1)	.095 (2.4)	0.935 (23.7)	560 (834)
192407	7	600	9 AWG	.045 (1.1)	.095 (2.4)	1.000 (25.4)	697 (1039)
192412	12	600	9 AWG	.045 (1.1)	.095 (2.4)	1.255 (31.9)	1079 (1608)
192603	3	600	6 AWG	.060 (1.5)	.095 (2.4)	0.985 (25.0)	623 (928)
192605	5	600	6 AWG	.060 (1.5)	.095 (2.4)	1.150 (29.2)	900 (1341)
199145	5	2000	14 AWG	.080 (2.0)	.095 (2.4)	0.990 (25.1)	484 (721)
199147	7	2000	14 AWG	.080 (2.0)	.095 (2.4)	1.065 (41.9)	584 (870)
199212	12	2000	14 AWG	.080 (2.0)	.110 (2.8)	1.375 (34.9)	903 (1345)
199219	19	2000	14 AWG	.080 (2.0)	.110 (2.8)	1.580 (40.1)	1241 (1849)
199105	5	2000	10 AWG	.080 (2.0)	.095 (2.4)	1.095 (27.8)	645 (961)
199107	7	2000	10 AWG	.080 (2.0)	.095 (2.4)	1.180 (30.0)	797 (1188)
199112	12	2000	10 AWG	.080 (2.0)	.110 (2.8)	1.535 (39.0)	1262 (1880)
199095	5	2000	9 AWG	.080 (2.0)	.095 (2.4)	1.135 (28.8)	716 (1067)
199097	7	2000	9 AWG	.080 (2.0)	.095 (2.4)	1.220 (31.0)	892 (1329)
199312	12	2000	9 AWG	.080 (2.0)	.110 (2.8)	1.595 (40.5)	1422 (2119)
199063	3	2000	6 AWG	.095 (2.4)	.095 (2.4)	1.145 (29.1)	746 (1112)
199065	5	2000	6 AWG	.095 (2.4)	.110 (2.8)	1.380 (35.1)	1108 (1651)

NOTE: Cushion layer is 47 mils • 1.2 mm thick for all cables. Part numbers are for solid conductor / 10 mil helical shield versions only.

Optional features available are: 1) Stranded conductors per ASTM B8; 2) Taped cushion layer.

The data herein is approximate and subject to normal manufacturing tolerances.

Information is subject to change without notice. Consult factory for a variety of alternate constructions for specific applications.