



Specialty Fiber



Issue date: 04/11
Supersedes: 02/10

Product Type: G.652.D ESMF 900 μm Buffer

Buffer Type: DuPont™ Hytrel®

Coating Type: Natural or ColorLock-XS

For the Telecommunication industry

- Active Optical Components
- Passive Optical Components
- Optical Wiring

Draka's 900 μm Buffer Enhanced Single-Mode Optical Fiber provides industry leading macro-bending performance in a small, versatile tight buffer. This fiber is available in standard fiber geometry and Draka's precision Patch Cord fiber geometry, for applications with stringent geometry requirements.




Value Innovation is a way of looking at the world. How we can help our customers do more, make more, save more, achieve more.

Features	Benefits
900 μm Tight Buffer	Flexible and durable allowing for easy handling
Compatible with ITU-T G.652.D	Meets most stringent industry fiber bending standards and is backwards compatible with existing single-mode fibers
Draka's Proprietary manufacturing process	Superior geometry, uniformity and homogeneity



ESMF



900 μm Buffer

G.652.D ESMF Tight Buffered Fiber
Product Type: G.652.D ESMF 900 µm Buffer
Buffer Type: DuPont™ Hytrel®
Coating Type: Natural or ColorLock-XS
Issue date: 04/11
Supersedes: 02/10
Optical Specifications
Attenuation¹

Attenuation Coefficient at 1310 nm	≤ 0.5 dB/km
Attenuation Coefficient at 1550 nm	≤ 0.5 dB/km

Geometrical Specifications

Parameters	Standard	Patchcord
Cladding Diameter	125 ± 0.7 µm	125 ± 0.4 µm
Core/Cladding Concentricity Error	≤ 0.5 µm	≤ 0.3 µm
Core/Cladding Non-Circularity	≤ 0.7 %	≤ 0.3 %
Coating Diameter	242 ± 7 µm	242 ± 5 µm
Coating/Cladding Concentricity Error	≤ 12 µm	≤ 10 µm
Coating Non-Circularity	≤ 5 %	≤ 5 %
Tight Buffer Diameter	900 ± 50 µm	900 ± 50 µm

Mechanical Specifications
Parameters

Fiber Proof Strength	≥ 100 kpsi ≥ 0.7 GPa
Minimum Bend Radius	20 mm

Environmental Specifications
Parameters

Operating Temperature	≥ - 20°C to ≤ + 80°C
Installation	≥ 0°C to ≤ + 50°C
Storage	≥ - 40°C to ≤ + 80°C

Fiber Types²

ESMF for normal applications

ESMF Patch Cord for applications requiring precise fiber geometry

Fibers available in Natural or ColorLock-XS coating

¹ Other attenuation levels available on request

² Refer to fiber datasheets for complete optical, geometrical, mechanical and environmental specifications

DuPont™ Hytrel® are registered trademarks or trademarks of E.I. du Pont de Nemours and Company or its affiliates.

How can we be of service to you?

Value Innovation is a way of looking at the world. How can we help our customers do more, make more, save more, achieve more?

Take DrakaElite™. Based on our proprietary manufacturing process and our control of all technological building blocks, we offer an extensive portfolio of specialized optical fibers that have been designed, developed, manufactured

and tested for every environment. Whether you want to guide, amplify, transmit, process, control or sense light, Draka has the fiber you need, whatever your environment. And if for some reason we don't have exactly what you need, well, we'll just make it.

That's Value Innovation in action.

Draka Communications

 fibersales@draka.com
 www.drakafiber.com | www.draka.com

The Draka Communications policy of continuous improvement may cause in changed specifications without prior notice