


DXPSS Short Span Self-Supporting Cable

chemical resistant / all-dielectric tray rated / loose tube construction / 2 to 144 fibers
singlemode or multimode / OFN



Applications

These are multiple fiber loose tube cables designed for high-speed interbuilding communication systems including long haul networking, interbuilding trunking and local loop applications, self supporting up to 1400 ft (427 m) depending on fiber count and loading conditions. A double jacket of heavy duty CPE resists attack by chemicals and petroleum derivatives. Loose tube design offers optimum fiber performance. These cables comply with IEEE P1222.

Fully flooded cables are available. All DXPSS cables are Gigabit Ethernet IEEE 802.3z compliant. MaxCap multimode fiber for 10 Gb networks is available.

Ratings

- OFN rated for indoor/outdoor
For sag and tension information, refer to the page at back of this section: DXPSS SHORT SPAN SELF-SUPPORTING CABLE CUST REF FO-100

Construction

FIBER: Multimode or singlemode fibers with an acrylate coating for mechanical protection colored per TIA/EIA 598.

BUFFER TUBES: Polymeric insulation filled with a moisture-resistant material to prevent water penetration. Fillers (when needed) are dielectric material.

CENTRAL STRENGTH MEMBER: Dielectric material (epoxy/fiberglass rod).

DRY BLOCK TAPE: Swellable tape wrapped around the cable core to prevent water penetration.

INNER JACKET: Black heavy duty CPE.

OUTER STRENGTH MEMBER: Multiple layers of high-strength aramid yarn.

OUTER JACKET: Black heavy duty CPE.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444
One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381

DXPSS Short Span Self-Supporting Cable

sag and tension data per NESC loading conditions

Part Number	Installation Pull Strength Lbs (Newtons)	Installation Bend Radius in (cm)	Operating Tension Lbs (Newtons)	Operating Bend Radius in (cm)	Maximum Recommended Span* feet (meters)	Cable O.D. in (mm)	Approx. Cable Weight Lbs/Mft (Kg/Km)
DXPSS2-02R-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS4-04-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS6-06-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS4-08-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS6-12-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS4-16-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS6-24-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS6-30-XXY	9000 (40071)	11.4 (29.1)	2500 (11130)	5.7 (14.6)	1000 (305)	0.572 (14.53)	125 (186)
DXPSS6-36-XXY	9000 (40071)	12.0 (30.5)	2500 (11130)	6.0 (15.2)	900 (274)	0.601 (15.27)	139 (207)
DXPSS12-48-XXY	9000 (40071)	12.5 (31.7)	2500 (11130)	6.2 (15.8)	900 (274)	0.624 (15.85)	146 (217)
DXPSS12-60-XXY	9000 (40071)	12.5 (31.7)	2500 (11130)	6.2 (15.8)	900 (274)	0.624 (15.85)	146 (217)
DXPSS12-72-XXY	9000 (40071)	13.2 (33.6)	2500 (11130)	6.6 (16.8)	800 (244)	0.661 (16.79)	163 (243)
DXPSS12-84-XXY	9000 (40071)	14.4 (36.5)	2500 (11130)	7.2 (18.2)	700 (213)	0.718 (18.24)	193 (287)
DXPSS12-96-XXY	9000 (40071)	15.5 (39.3)	2500 (11130)	7.7 (19.7)	600 (183)	0.774 (19.66)	227 (338)
DXPSS12-108-XXY	9000 (40071)	16.2 (41.2)	2500 (11130)	8.1 (20.6)	600 (183)	0.811 (20.60)	250 (372)
DXPSS12-120-XXY	9000 (40071)	17.4 (44.2)	2500 (11130)	8.7 (22.1)	500 (152)	0.870 (22.10)	290 (432)
DXPSS12-132-XXY	9000 (40071)	18.1 (46.1)	2500 (11130)	9.1 (23.0)	500 (152)	0.907 (23.04)	316 (470)
DXPSS12-144-XXY	9000 (40071)	18.5 (46.9)	2500 (11130)	9.2 (23.4)	400 (122)	0.923 (23.44)	353 (525)

*Maximum span recommendations are per NESC light loading conditions. Long span and microspan versions available.

Flooded core is available. Higher fiber counts are available.

The data herein is approximate and subject to normal manufacturing tolerances.

Information is subject to change without notice. Consult factory for a variety of alternate constructions for specific applications.

Fiber Performance

Replace XXY in the part number above with your fiber requirements:

Multi-mode	Min Bandwidth	Max. Attenuation
Designation	850nm/1300nm	850nm/1300nm
50GBE	1500/500	3.50/1.50
50H	500/500	3.50/1.50
50E1 (HiCap)	500/500	3.50/1.00
62X	200/500	3.50/1.00
62E1	300/600	3.50/1.00*

* Mode conditioning patch cords not required

Singlemode	Max. Attenuation
Designation	1310nm/1550nm
010X	0.40/0.30
010A3	0.35/0.25

Environmental Specifications

Description	FOTP	Requirements
Operating Temp	EIA-455-3	-40°C to 70°C
Storage Temp	EIA-455-3	-40°C to 70°C
Installation Temp	- - -	-20°C to 80°C

Mechanical Specifications

Description	FOTP	Requirements
Crush Resistance	EIA-455-41	1000 N/cm (575 lbs/in)
Impact Resistance	EIA-455-25	25 impacts with 5.0 N-m
Cyclic Flexing Test	EIA-455-104	2000 cycles

© DRAKA - A Brand of The Prysmian Group. 2012 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued June 2012.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444
 One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381