



Specialty Fiber



Issue date: 04/11

Supersedes: --/--

For the Telecommunication industry

- Active Optical Components
- Passive Optical Components
- Optical Wiring

Product Type: BendBright-XS 900 µm PVDF

Buffer Type: 900 µm PVDF

Coating Type: Natural or ColorLock-XS

Draka's PVDF 900 µm BendBright-XS Optical Fiber provides industry leading macro-bending performance in a small, versatile tight buffer. This fiber is available in standard fiber geometry and Draka's precision Patch Cord fiber geometry, for applications with stringent geometry requirements.




Value Innovation is a way of looking at the world. How we can help our customers do more, make more, save more, achieve more.



Features	Benefits
900 µm PVDF Tight Buffer	<ul style="list-style-type: none"> • Flexible and durable allowing for easy handling • Excellent chemical resistance • Excellent high and low temperature resistance
UL-94 Flammability Test Class V-0	Excellent flame and smoke resistance
Extremely low bend loss	Allows for small bend radii for tight space applications
Compatible with ITU-T G.657.A2 & G.657.B2 and G.652.D	Exceeds industry bending requirements and is backwards compatible with existing single-mode fibers
Draka's Proprietary manufacturing process	Superior geometry, uniformity and homogeneity

BendBright-XS



900 µm PVDF

Truly Bend-Insensitive Tight Buffered Fiber
Product Type: BendBright-XS 900 µm PVDF
Buffer Type: 900 µm PVDF
Coating Type: Natural or ColorLock-XS
Issue date: 04/11
Supersedes: --/--
Optical Specifications

Attenuation ¹	Specified Value
Attenuation Coefficient at 1310 nm	≤ 0.7 dB/km
Attenuation Coefficient at 1550 nm	≤ 0.7 dB/km

Geometrical Specifications

Parameters	Standard	Patchcord
Cladding Diameter	125 ± 0.7 µm	125 ± 0.4 µm
Core/Cladding Concentricity Error	≤ 0.5 µm	≤ 0.3 µm
Core/Cladding Non-Circularity	≤ 0.7 %	≤ 0.3 %
Coating Diameter	242 ± 7 µm	242 ± 5 µm
Coating/Cladding Concentricity Error	≤ 12 µm	≤ 10 µm
Coating Non-Circularity	≤ 5 %	≤ 5 %
Tight Buffer Diameter	900 ± 50 µm	900 ± 50 µm

Mechanical Specifications

Parameters	Specified Value
Fiber Proof Strength	≥ 100 kpsi ≥ 0.7 GPa

Environmental Specifications

Parameters	Specified Value
Operating Temperature	≥ - 20°C to ≤ + 85°C
Installation	≥ 0°C to ≤ + 50°C
Storage	≥ - 40°C to ≤ + 85°C

Fiber Types²

BendBright-XS for normal applications

BendBright-XS Patch Cord for applications requiring precise fiber geometry

Fibers available in Natural or ColorLock-XS coating

¹ Other attenuation levels available on request

² Refer to fiber datasheets for complete optical, geometrical, mechanical and environmental specifications

How can we be of service to you?

Value Innovation is a way of looking at the world. How can we help our customers do more, make more, save more, achieve more?

Take DrakaElite™. Based on our proprietary manufacturing process and our control of all technological building blocks, we offer an extensive portfolio of specialized optical fibers that have been designed, developed, manufactured

and tested for every environment. Whether you want to guide, amplify, transmit, process, control or sense light, Draka has the fiber you need, whatever your environment. And if for some reason we don't have exactly what you need, well, we'll just make it.

That's Value Innovation in action.

Draka Communications

fibersales@draka.com
www.drakafiber.com | www.draka.com

The Draka Communications policy of continuous improvement may cause in changed specifications without prior notice