


Hydroline™ -LDP Submersible Pump Cable

Light duty / parallel construction / 14 to 4 AWG / PVC insulation / 600 volt



Applications

Hydroline™-LDP submersible pump cables are specially designed for rugged applications, improved stripability and ease of conductor separation, for use within well casing to supply power to the submersible pump.

Draka's Hydroline pump cables are formulated with RoHS compliant materials. Operating temperature range is between -25° and +75°C. The features listed below are standard items; they may be modified per your request and need. Please contact for details.

Specifications

- UL Type THHN or THWN conforming to UL Standard 83
- RoHS compliant

Construction

CONDUCTOR: Bare annealed copper per ASTM B3, Class C concentrically stranded per ASTM B8.

INSULATION: Heat and moisture resistant polyvinyl chloride (PVC).

TYPICAL CIRCUIT IDENTIFICATION: Insulation coded in accordance with NEMA WC-57 (black, red, yellow, green).

ASSEMBLY: Insulated circuit and ground conductors are assembled flat and paralleled.

SURFACE MARKING: The jacket surface shall be printed or indented with: DRAKA PA HYDROLINE-LDP SUBMERSIBLE PUMP CABLE "number and size of conductors" THW CDRS 600V (UL).

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com
One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381

Hydroline™ -LDP Submersible Pump Cable

Light duty / parallel construction / 14 to 4 AWG / PVC insulation / 600 volt

Part Number	Conductor Number / AWG	Ground AWG	Stranding	Insulation Thickness in (mm)	Nylon Thickness in (mm)	Jacket Thickness in (mm)	Cable Weight Lbs/Mft (Kg/Km)
LDP14-3	3 / #14	-	19	.045 (1.1)	-	-	71 (106)
LDP12-3	3 / #12	-	19	.045 (1.1)	-	-	99 (147)
LDP10-3	3 / #10	-	19	.045 (1.1)	-	-	142 (211)
LDP08-3	3 / #8	-	19	.060 (1.5)	-	-	230 (342)
LDP06-3	3 / #6	-	19	.060 (1.5)	-	-	343 (510)
LDP04-3	3 / #4	-	19	.060 (1.5)	-	-	500 (744)
LDP14-2G	2 / #14 + Grd	14	19	.045 (1.1)	-	-	71 (106)
LDP14-3G	3 / #14 + Grd	14	19	.045 (1.1)	-	-	95 (141)
LDP12-2G	2 / #12 + Grd	12	19	.045 (1.1)	-	-	99 (147)
LDP12-3G	3 / #12 + Grd	12	19	.045 (1.1)	-	-	132 (196)
LDP10-2G	2 / #10 + Grd	10	19	.045 (1.1)	-	-	142 (211)
LDP10-3G	3 / #10 + Grd	10	19	.045 (1.1)	-	-	189 (281)
LDP08-3G	3 / #8 + Grd	10	19	.060 (1.5)	-	-	277 (412)
LDP06-3G	3 / #6 + Grd	8	19	.060 (1.5)	-	-	420 (625)
LDP04-3G	3 / #4 + Grd	8	19	.060 (1.5)	-	-	577 (859)

The data herein is approximate and subject to normal manufacturing tolerances.

Information is subject to change without notice. Consult factory for a variety of alternate constructions for specific applications.

© DRAKA - A Brand of The Prysmian Group. 2013 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued February 2013.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com

One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381