


Crane Spreader Reeling Cable

75° C to -40° C / 600V



Applications

CRANE SPREADER REELING CABLE is specifically designed and manufactured to withstand abusive environments, high hoist and trolley speeds and extreme mechanical stresses predominant on vertical reeling systems found in new generation ship to shore container cranes.

Specifications and Ratings

- Rated for continuous operation at 75° C to -40° C in wet or dry locations

Construction Options

Consult factory for cables designed and manufactured in a variety of alternative constructions for specific applications.

Options include:

- Composite conductors
- Fiber optic components

Kevlar® is a registered trademark of E I DuPont DeNemours and Company.

Design Parameters

CONDUCTORS: Flexible stranding, soft-drawn tinned copper; per ASTM B-33, ASTM B-172, and UL-62 for flexibility, extended flex life and reduced copper fatigue/conductor breakage.

INSULATION: Black and numbered torsion-resistant insulation for excellent physical and electrical properties.

CABLING: Conductors are cabled with non-wicking, non-hygroscopic fillers with an overall binder tape for increased mechanical strength/impact resistance and exceptional performance in severe flexing applications.

JACKET: A double layer Kevlar® reinforced jacket provides core stability at temperatures ranging from 75° C to -40° C. Kevlar reinforcing improves the cable's overall strength while increasing torsion resistance.



© DRAKA - A Brand of The Prysmian Group. 2012 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued June 2012.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com

Crane Spreader Reeling Cable

75° C to -40° C / 600V

Part Number	Conductor Number	Conductor Size AWG (mm ²)	Stranding	Insulation Thickness in (mm)	Jacket Thickness in (mm)	Nominal Cable O.D. in (mm)	Ampacity ¹	Minimum Bend Radius in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)	Max. Safe Reeling Tension lbs. (N)
030889	24	12 (3.5)	19	0.025 (0.64)	0.140 (3.56)	1.240 (31.5)	17	14.9 (378.0)	867 (1291)	1100 (4893)
030890	30	12 (3.5)	19	0.025 (0.64)	0.140 (3.56)	1.310 (33.3)	14	15.7 (399.3)	1092 (1626)	1100 (4893)
030829	36	12 (3.5)	19	0.025 (0.64)	0.160 (4.06)	1.455 (37.0)	14	17.5 (443.5)	1345 (2003)	1100 (4893)
030892	44	12 (3.5)	19	0.025 (0.64)	0.160 (4.06)	1.560 (39.6)	12	18.7 (475.5)	1550 (2308)	1400 (6228)
030893	56	12 (3.5)	19	0.025 (0.64)	0.160 (4.06)	1.660 (42.2)	12	19.9 (506.0)	1880 (2798)	1400 (6228)
Composite Cables										
031022	12 + 38	12/14 (3.5/2.5)	19	0.025 (0.64)	0.160 (4.06)	1.600 (40.6)	12/9	18.8 (478.5)	1413 (2104)	1400 (6228)

¹Ratings apply to a single cable in free air 30° C ambient, 75 °C conductor temperature, installed on mono-spiral reels or single layer level wind reels.

Values include 50% load diversity.

© DRAKA - A Brand of The Prysmian Group. 2012 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued June 2012.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | www.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444 | www.drakausa.com