


## Underground Signal Cable

Multiple EPR insulated conductors | 14, 10, 9, and 6 AWG / PE jacket / 600 and 2000 volt



### Applications

These are multi-conductor 600 and 2000 volt signal cables specifically designed for use in railroad signal and control circuits in accordance with the AREMA Signal Manual. They are intended for buried installation for use wherever long service life is required. They consist of ethylene propylene rubber (EPR) insulated conductors and a polyethylene outer jacket.

### Specifications and Ratings

- AREMA Signal Parts 10.3.16, 10.3.19, 10.3.21
- ICEA S-95-658 (NEMA WC70)

### Design Parameters

**CONDUCTOR:** Solid soft drawn, bare or tinned copper per ASTM B258 and B33.

**INSULATION:** Heat and moisture resistant EPR meeting the requirements of AREMA C&S Manual Part 10.3.19, suitable for a maximum continuous operating temperature of 90°C.

**CIRCUIT IDENTIFICATION:** Black conductors with number print: (1-ONE, 2-TWO, 3-THREE, etc.). One conductor with an identifying red stripe serves as a tracer.

**ASSEMBLY:** The insulated circuit conductors are cabled together with non-hygroscopic fillers as needed. The cable core is wrapped in a binder tape.

**OVERALL JACKET:** Heat and moisture-resistant black polyethylene (PE) meets the requirements of AREMA C&S Manual Part 10.3.21. Neoprene and LSZH XLPO are available. Optional ripcord placed underneath the overall jacket is available upon request.

### Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | website: [na.prysmiangroup.com](http://na.prysmiangroup.com)

### Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444  
One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381



A brand of the



# Underground Signal Cable

Multiple EPR insulated conductors | 14, 10, 9, and 6 AWG / PE jacket / 600 and 2000 volt

Part Number	Number of Conductors	Rated Voltage	Conductor Size	Average Insulation Thickness in (mm)	Average Jacket Thickness in (mm)	Cable O.D. in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
191105	5	600	14AWG	.060 (15)	.080 (2.0)	0.730 (18.5)	224 (334)
191107	7	600	14AWG	.060 (15)	.080 (2.0)	0.790 (20.1)	289 (431)
191112	12	600	14AWG	.060 (15)	.095 (2.4)	1.050 (26.7)	486 (724)
192119	19	600	14AWG	.060 (15)	.095 (2.4)	1.225 (31.1)	712 (1061)
191305	5	600	10AWG	.060 (15)	.080 (2.0)	0.830 (21.1)	353 (526)
191307	7	600	10AWG	.060 (15)	.095 (2.4)	0.935 (23.7)	465 (693)
191312	12	600	10AWG	.060 (15)	.095 (2.4)	1.210 (30.7)	789 (1176)
191405	5	600	9AWG	.060 (15)	.080 (2.0)	0.870 (22.1)	411 (612)
191407	7	600	9AWG	.060 (15)	.095 (2.4)	0.980 (24.9)	545 (812)
191412	12	600	9AWG	.060 (15)	.095 (2.4)	1.270 (32.3)	928 (1383)
191603	3	600	6AWG	.080 (2.0)	.095 (2.4)	0.960 (24.4)	379 (565)
191605	5	600	6AWG	.080 (2.0)	.095 (2.4)	1.145 (29.1)	621 (925)
198145	5	2000	14AWG	.095 (2.4)	.095 (2.4)	0.960 (24.4)	344 (513)
198147	7	2000	14AWG	.095 (2.4)	.095 (2.4)	1.040 (26.4)	443 (660)
198212	12	2000	14AWG	.095 (2.4)	.110 (2.8)	1.390 (35.3)	741 (1044)
198219	19	2000	14AWG	.095 (2.4)	.110 (2.8)	1.620 (41.1)	1085 (1617)
198105	5	2000	10AWG	.095 (2.4)	.095 (2.4)	1.060 (26.9)	487 (726)
198107	7	2000	10AWG	.095 (2.4)	.095 (2.4)	1.155 (29.3)	637 (949)
198112	12	2000	10AWG	.095 (2.4)	.110 (2.8)	1.550 (39.4)	1075 (1602)
198095	5	2000	9AWG	.095 (2.4)	.095 (2.4)	1.100 (27.9)	551 (821)
198097	7	2000	9AWG	.095 (2.4)	.095 (2.4)	1.200 (30.4)	725 (1080)
198312	12	2000	9AWG	.095 (2.4)	.110 (2.8)	1.610 (40.9)	1226 (1827)
198063	3	2000	6AWG	.110 (2.8)	.095 (2.4)	1.095 (27.8)	565 (842)
198065	5	2000	6AWG	.110 (2.8)	.110 (2.8)	1.350 (34.3)	905 (1348)

Information is subject to change without notice. Consult factory for a variety of alternate constructions for specific applications. Optional features available are: 1) Stranded conductors per ASTM B8.

© DRAKA - A Brand of The Prysmian Group. 2017 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued November 2017.

**Prysmian Group**  
**700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | website: [na.prysmiangroup.com](http://na.prysmiangroup.com)**  
**Sales and Distribution:**  
**22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444**  
**One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381**