


## CUBOND Control Cable

multiple XHHW-2 conductors / 14, 12 & 10 AWG / copper shield / CPE jacket / 600 volt



### Applications

These are multiple conductor control tray cables with crosslinked (thermoset) polyethylene (XLPE) insulation and a crosslinked (thermoset) chlorinated polyethylene (CPE) or polychloroprene (PCP) jacket. These cables are suitable for use in cable trays, direct burial or aerial installations.

### Specifications and Ratings

- UL Standard 44 and 1277 Type TC power and control cable
- ICEA S-73-532 (NEMA WC 57)
- IEEE 383
- UL Direct Burial
- UL Sunlight Resistant
- UL Oil Resistant
- -40°C

### Design Parameters

**CONDUCTORS:** Class B (7 strand), soft drawn, bare or tinned copper per ASTM B3, ASTM B8 and ASTM B33.

**INSULATION:** Crosslinked polyethylene (XLPE) that meets ICEA S-73-532 (NEMA WC 57) & UL 44 acceptable for 90°C wet and dry locations.

**CIRCUIT IDENTIFICATION:** Appendix E, Method 1, Table E-1 or E-2 of ICEA S-73-532 (NEMA WC 57).

**ASSEMBLY:** Individual conductors are cabled with non-hygroscopic fillers where necessary to form a round compact core and wrapped with a binder of polyester tape.

**JACKET:** Black sunlight-resistant, flame-retardant, chlorinated polyethylene (CPE) or polychloroprene (PCP) that meets UL 1277.

### Prysmian Group

4 Tesseneer Drive | Highland Heights, KY 41076 | +1 859-572-8000 | [www.na.prysmiangroup.com](http://www.na.prysmiangroup.com)

### Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764  
One Tamaqua Blvd. | Schuylkill Haven PA 17972

## CUBOND Control Cable

multiple XHHW-2 conductors / 14, 12 & 10 AWG / copper shield / CPE jacket / 600 volt

Number/Size of Conductors	Number of Strands	Ground Size AWG	Insulation Thickness in (mm)	Average Jacket Thickness in (mm)	Cable O.D. in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
2 / 14 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.385 (9.78)	77 (115)
3 / 14 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.400 (10.2)	89 (132)
4 / 14 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.445 (11.3)	123 (183)
5 / 14 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.485 (12.3)	135 (201)
7 / 14 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.525 (13.3)	190 (283)
9 / 14 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.650 (16.5)	263 (391)
12 / 14 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.720 (18.3)	337 (501)
19 / 14 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.840 (21.3)	495 (737)
2 / 12 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.420 (10.7)	99 (147)
3 / 12 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.445 (11.3)	130 (193)
4 / 12 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.490 (12.4)	164 (244)
5 / 12 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.535 (13.6)	185 (275)
7 / 12 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.615 (15.6)	260 (387)
9 / 12 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.710 (18.0)	350 (521)
12 / 12 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.800 (20.3)	425 (632)
19 / 12 AWG	7	-	0.030 (0.76)	0.080 (2.03)	0.975 (24.8)	669 (995)
2 / 10 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.470 (11.9)	132 (196)
3 / 10 AWG	7	-	0.030 (0.76)	0.045 (1.54)	0.500 (12.7)	179 (266)
4 / 10 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.580 (14.7)	247 (368)
5 / 10 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.635 (16.1)	279 (415)
7 / 10 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.690 (17.5)	368 (548)
9 / 10 AWG	7	-	0.030 (0.76)	0.060 (1.52)	0.805 (20.4)	521 (775)
12 / 10 AWG	7	-	0.030 (0.76)	0.080 (2.03)	0.945 (24.0)	642 (955)
19 / 10 AWG	7	-	0.030 (0.76)	0.080 (2.03)	1.105 (28.1)	946 (1408)
3 / 8 AWG	7	10 AWG	0.045 (1.54)	0.060 (1.52)	0.650 (16.5)	321 (478)
3 / 6 AWG	7	8 AWG	0.045 (1.54)	0.060 (1.52)	0.735 (18.7)	460 (684)
3 / 4 AWG	7	8 AWG	0.045 (1.54)	0.080 (2.03)	0.910 (23.1)	671 (998)
3 / 2 AWG	7	6 AWG	0.045 (1.54)	0.080 (2.03)	1.050 (26.7)	991 (1475)
3 / 1/0 AWG	19	6 AWG	0.055 (1.40)	0.080 (2.03)	1.240 (31.5)	1470 (2187)
3 / 2/0 AWG	19	6 AWG	0.055 (1.40)	0.080 (2.03)	1.340 (34.0)	1789 (2662)
3 / 4/0 AWG	19	4 AWG	0.055 (1.40)	0.080 (2.03)	1.580 (40.1)	2676 (3982)
3 / 250 KCMIL	37	4 AWG	0.065 (1.65)	0.110 (2.79)	1.840 (46.7)	3227 (4802)
3 / 350 KCMIL	37	3 AWG	0.065 (1.65)	0.110 (2.79)	2.030 (51.6)	4320 (6428)
3 / 500 KCMIL	37	2 AWG	0.065 (1.65)	0.110 (2.79)	2.320 (58.9)	6003 (8932)

Optional features available are: 1) Flexible stranded conductors; 2) Tin-coated copper conductors per ASTM B33; 3) Flame-retardant ethylene propylene rubber (FREP) insulated conductors; 4) 2000 volt rating; 5) Aluminum shield.

The data herein is approximate and subject to normal manufacturing tolerances. These specifications are subject to change without notice.

Consult factory for a variety of alternate constructions for specific applications.

© DRAKA - A Brand of The Prysmian Group. 2018 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued December 2018.

### Prysmian Group

4 Tesseneer Drive | Highland Heights, KY 41076 | +1 859-572-8000 | [www.na.prysmiangroup.com](http://www.na.prysmiangroup.com)

### Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764

One Tamaqua Blvd. | Schuylkill Haven PA 17972