


## Traction Power Cable LSZH MV-90 2.4KV

Single conductor / EPR insulated / XLPO jacket / 4/0 AWG to 1000 KCMIL / 2400 volt



### Applications

These are single conductor 2.4KV power cables where low-smoke non-halogen cables are required, in areas requiring NFPA 130 compliance. They consist of an extruded thermosetting semiconducting conductor shield, an ethylene propylene rubber insulated conductor jacketed with a tough low smoke zero halogen (LSZH) crosslinked polyolefin (XLPO) jacket. They are highly heat, oil and moisture-resistant, extremely tough yet flexible, and can sustain 90°C wet or dry operating temperatures. A shielded version is available as well.

### Physical Characteristics

Jacket Color: Black

### Specifications

Conductor: ASTM B 3 and ASTM B 8  
UL 1072, NFPA 130, IEEE 383, IEEE 1202, UL-1685  
UL listed

### Ratings

Voltage: 2400 Volts  
Temperature: 90°C Wet or Dry

### Components

- A: Class B stranded, bare copper conductor  
Options: Class B solid, Class C, D, G and H stranded  
tinned or bare.
- B: Semi-conducting thermoset extruded conductor shield
- C: Ethylene Propylene Rubber (EPR) Insulation
- D: Heat and moisture resistant, thermosetting,  
Low-Smoke Zero Halogen (LSZH), black cross-linked  
polyolefin (XLPO) jacket

### Packaging

Non-returnable wood reels

### Print Legend

PRYSMIAN-T TRACTION POWER CABLE "SIZE OF  
CONDUCTOR" 2400V NONSHIELDED MV-90 (UL) 90C WET  
OR DRY SUN RES FT4 ST1 FOR CT USE (MONTH/YEAR)  
SEQUENTIAL FOOTAGE

### Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | [na.prysmiangroup.com](http://na.prysmiangroup.com)

### Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444  
One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381



A brand of the

**Prysmian**  
Group

## Traction Power Cable LSZH MV-90 2.4KV

Single conductor / EPR insulated / XLPO jacket / 4/0 AWG to 1000 KCMIL / 2400 volt

Conductor Size	Stranding	Average Insulation Thickness in (mm)	Average Jacket Thickness in (mm)	Minimum Bend Radius in (cm)	Ampacity* 90°C	Cable O.D in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
4/0 AWG	19	0.125" (3.18)	0.095" (2.41)	6.5" (16.51)	400	1.02" (25.91)	1033 (1538)
500 KCMIL	37	0.140" (3.56)	0.110" (2.79)	8.5" (21.59)	695	1.35" (34.29)	2117 (3151)
750 KCMIL	61	0.155" (3.94)	0.125" (3.18)	9.6" (24.38)	900	1.60" (40.64)	3100 (4614)
1000 KCMIL	61	0.155" (3.94)	0.125" (3.18)	10.5" (26.67)	1075	1.75" (44.45)	3971 (5910)

\*Ampacity based on ambient air temperature of 30°C in free air

\*Representative spec - Draka manufactures to all transit and railroad specifications accordingly.

The data herein is approximate and subject to normal manufacturing tolerances.

Information is subject to change without notice. Consult factory for a variety of alternate constructions for specific applications.

© DRAKA - A Brand of The Prysmian Group. 2012 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued June 2012.

### Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | [na.prysmiangroup.com](http://na.prysmiangroup.com)

### Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444

One Tamaqua Blvd. | Schuylkill Haven PA 17972 | Tel +1-570-385-4381